

**Garant**
**Boring bar carbide, left-hand, Shank  $\varnothing$  / insert size: 20/11 mm**

**Order data**

Order number	261113 20/11
GTIN	4062406398057
Item class	21T

**Technical description**

suitable indexable insert	VB.. 1103..
Setting angle $\kappa$	142 degrees
Minimum pre-drill $\varnothing D_{\min}$	24 mm
Pack of insert screws	269028 7
Centre offset $L_3$	2 mm
ISO code toolholder	E20S SVJBR/L 11
Insert size	11 mm
Overall length L	250 mm
Head length $L_1$	38 mm
Clamping height $L_2$	19 mm
Neck width $L_4$	11 mm
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 7	269028 7
-----------------------------	----------