



Dynafile® pneumatic belt linisher, Type: 15302



Order data

Order number	079551 15302
GTIN	616026153028
Item class	03R

Description

Version:

Versatile machines with **adjustable linishing belt guides, exactly true-running belts**, and with an exchangeable **contact arm** allowing the use of contact wheel or side face. The composite linishing belt coating enables **quick** and **easy change of the linishing belt**. The **linishing belt** cooling via the exhaust air prolongs the working life of the belts. Adjustable handle **Dynafile® III, powerful 520 W** linisher for high removal rates, **surface preparation set, adjustable linishing head** with additional support handle. Linishing belt dimensions 6, 13, 19, 25×457 mm.

Application:

For abrading, deburring, blending, finishing and polishing, ideal also for flexible access to difficult places.

Supplied with:

Including the necessary coupling adaptors.

Note:

Other contact arm versions for Dynafile® from No. 079559 available on request or in our eShop.

Technical description

Output power	522 W
--------------	-------

Operating noise	87 dB(A)
maximum vibration to EN	< 2.5 m/s ²
Tape width	6; 13; 19; 25; mm
Manufacturer's designation	Dynafile III kit
maximum air consumption	906 l/min
maximum speed	20000 min ⁻¹
Band length	457 mm
Weight	1.1 kg
Model range	Dynafile III
Compressed air connection	1/4 in
Connection thread	NPT
Packaging	Carrying case
Type of product	Linishing machine

Accessories

Contact arm for Dynafile® III Type 15350	079561 15350
Contact arm for Dynafile® III Type 15357	079561 15357
Contact arm for Dynafile® III Type 15321	079561 15321