

**STEMI 305 stereo microscope with camera output, Type: 305TRINO**

Order data

Order number	491836 305TRINO
GTIN	2050001932624
Item class	49B

Description**Version:**

Stereo microscope for high resolution, intensely illuminated sharp focus images. Greenough design for the best image quality. **Integral vertical LED light source.** Individually adjustable and compensates for eye spacing and short-sightedness. Carrying handle for mobile use. Cold light stand, adjustable incident light, flat transillumination base (bright field / dark field), column with drive and 145 mm length of travel. With additional K LED spotlight with light beam adjustable for zoom and height. With integral C-Mount camera output.

Optional extras:

AxioCam 491852 and 491853

Polarisation accessories for spotlighting and transillumination.

Attachment lenses 0.75× / 1.5× / 2.0× available on request.

Note:

Available as options: Version with integral Wi-Fi camera and router. Version without transillumination unit.

Magnification (x-times): 8 - 40

Zoom: 5: 1

Field of vision Ø: 29 mm

Eyepiece: PL 10×

Working distance: 110 mm

Technical description

Zoom	5: 1
Eyepiece	PL 10×
Field of vision Ø	29 mm
Working distance	110 mm
Magnification (x-times)	8 - 40
Power supply	Mains operated
Type of product	Stereo microscope

Accessories

AxioCam microscope camera 105 colour Type 105C	491853 105C
Eyepieces, pair	491832
AxioCam ERc5s microscope camera Type ERC5S2	491852 ERC5S2