

**Garant**

**Sandals, anthracite/black Comfort ESD S1P W1 safety sandals, EU shoe size: 40**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 092054 40     |
| GTIN         | 4062406400262 |
| Item class   | 01S           |

**Description****Version:**

GARANT comfort safety shoes combine the highest possible wearing comfort with modern design. Innovative and high-quality materials coupled with outstandingly high-quality "Made in Germany" workmanship guarantee maximum protection combined with minimum weight. The different widths and tweaked manufacturing technique permit a "true" multi-width system and thus the ideal solution for different widths of feet. The rigorous implementation of ergonomic principles and exchangeable weight-dependent shock absorption significantly reduce stress on the knee and back, and thus contribute to long-term health.

- **The material of the uppers is light-weight but hard-wearing micro-fibre.**
- **Breathable functional lining.**
- **Practical GARANT comfort heel-puller allows the shoes to be taken off quickly and easily.**
- **GARANT comfort insoles with weight-dependent shock absorption.**
- **GARANT comfort TPU outer sole.**
- **Protection against electrostatic discharge (ESD).**

Sandals with large-area ventilation structure and textile penetration protection.

**Standard:**

EN ISO 20345:2011 S1P SRC

**Note:**

- **GARANT comfort insoles with weight-dependent damping: 092864 (soft), 092865 (medium), 092866 (hard).**

- **Shoe sizes 36-39 are supplied as standard with soft damping, sizes 40-45 with medium damping, and sizes 46-48 with hard damping.**
- **Matching GARANT laces for lace-up boots: 092855 120, quick-release fastener for the sandals: 092856 55 (sizes 36-41) and 092856 65 (sizes 42-48).**

Wide fitting W2, see No. 092055.

electrostatic characteristic: EGB/ESD

Protection class: S1P

Material of protective toe-cap: Aluminium

Puncture resistance: Tekstil

Standard: Inlay type-tested according to DGUV regulation 191

Characteristics: Vario® damping

## Technical description

|                                |  |
|--------------------------------|--|
| Puncture resistance            | Tekstil  |
| EU shoe size                   | 40   |
| Standard                       | Inlay type-tested according to DGUV regulation 191 |
| Characteristics                | Vario® damping                                     |
| Protection class               | S1P  |
| Gender                         | Gentlemen's  |
| Material of protective toe-cap | Aluminium  |
| electrostatic characteristic   | EGB/ESD  |
| Type of product                | Safety sandals                                     |