

## Garant

**Lace-up boots, anthracite/black Comfort ESD S3 W2 safety lace-up boots, EU shoe size: 48**



### Order data

Order number	092075 48
GTIN	4062406400736
Item class	01S

### Description

#### Version:

GARANT comfort safety shoes combine the highest possible wearing comfort with modern design. Innovative and high-quality materials coupled with outstandingly high-quality "Made in Germany" workmanship guarantee maximum protection combined with minimum weight. The different widths and tweaked manufacturing technique permit a "true" multi-width system and thus the ideal solution for different widths of feet. The rigorous implementation of ergonomic principles and exchangeable weight-dependent shock absorption significantly reduce stress on the knee and back, and thus contribute to long-term health.

- **The material of the uppers is light-weight but hard-wearing micro-fibre.**
- **Breathable functional lining.**
- **Practical GARANT comfort heel-puller allows the shoes to be taken off quickly and easily.**
- **GARANT comfort insoles with weight-dependent shock absorption.**
- **GARANT comfort TPU outer sole.**
- **Protection against electrostatic discharge (ESD).**

Boots with seam-free construction. Dust flap. Protection against water penetration.

#### Standard:

EN ISO 20345:2011 S3 SRC

#### Note:

Narrow fitting W1, see No. 092074.

- **GARANT See accessories for foot protection for the comfort insoles with weight-dependent shock absorption, under: 092864 (soft), 092865 (medium), 092866 (hard).**
- **Shoe sizes 36-39 are supplied as standard with soft shock absorption, sizes 40-45 with medium shock absorption, and sizes 46-48 with hard shock absorption.**
- **See accessories for foot protection for the appropriate GARANT laces for lace-up boots under: 092855 120 and the quick-release fastener for sandals; 092856 55 (sizes 36-41) and 092856 65 (sizes 42-48).**

electrostatic characteristic: EGB/ESD

Protection class: S3

Material of protective toe-cap: Aluminium

Puncture resistance: Tekstil

Standard: Inlay type-tested according to DGUV regulation 191

Characteristics: Vario® damping

## Technical description

Material of protective toe-cap	Aluminium
Characteristics	Vario® damping
Puncture resistance	Tekstil
Protection class	S3
EU shoe size	48
Gender	Gentlemen's
Standard	Inlay type-tested according to DGUV regulation 191
electrostatic characteristic	EGB/ESD
Type of product	Safety boots