

Garant**Double clamping pot, Type: 120****Order data**

Order number	360028 120
GTIN	4045197812827
Item class	310

Description**Version:**

The zero point clamping of the GARANT ZeroClamp system is an important function for modern production systems, especially in automated production. Thanks to a special contact interface, it ensures precise and reliable zero point repetition accuracy. The pneumatic clamping force of the system holds workpieces securely in the desired position, making it possible to change workpieces quickly and accurately without repositioning. This reduces the set-up effort and increases productivity. The zero point clamping of the GARANT ZeroClamp system is indispensable for efficient production processes. Find out more about the innovative technology from GARANT ZeroClamp and optimise your production.

Application:

For free positioning of the double-ended clamping pot on grid plates, clamping towers etc. In this way you turn a threaded socket on your grid plate into a defined zero point / reference point!

Supplied with:

2 clamping pots, 2 coupling plugs.

Optional extras:

Clamping stud No. 360025.

Note:

Further heights up to 200 mm available on request.

Technical description

Height H	100 mm
Indexing hole available	yes
Holding force	25 kN
Clamping pot \varnothing d	120 mm
Series	ZeroClamp
Type of product	Clamping pot