

Garant**Double clamping pot, Type: 138****Order data**

Order number	360028 138
GTIN	4045197812834
Item class	310

Description**Version:**

The zero point clamping of the GARANT ZeroClamp system is an important function for modern production systems, especially in automated production. Thanks to a special contact interface, it ensures precise and reliable zero point repetition accuracy. The pneumatic clamping force of the system holds workpieces securely in the desired position, making it possible to change workpieces quickly and accurately without repositioning. This reduces the set-up effort and increases productivity. The zero point clamping of the GARANT ZeroClamp system is indispensable for efficient production processes. Find out more about the innovative technology from GARANT ZeroClamp and optimise your production.

Application:

For free positioning of the double-ended clamping pot on grid plates, clamping towers etc. In this way you turn a threaded socket on your grid plate into a defined zero point / reference point!

Supplied with:

2 clamping pots, 2 coupling plugs.

Optional extras:

Clamping stud No. 360025.

Note:

Further heights up to 200 mm available on request.

Technical description

Indexing hole available	yes
Height H	150 mm
Clamping pot \varnothing d	138 mm
Holding force	40 kN
Series	ZeroClamp
Type of product	Clamping pot