

## Flat magnet with internal thread, Ferrite, Ø: 63mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 085915 63     |
| GTIN         | 2050000965302 |
| Item class   | 08Q           |

### Description

#### Version:

- **Shielded flat magnet made of hard ferrite with insert nut.**
- **Galvanised surface.**
- **Temperature-resistant up to maximum 120 °C.**

#### Application:

For clamping, assembling, incorporation by screw fastening.

#### Note:

Screw-in hooks with external thread under No. 085921.

### Technical description

|                                |            |
|--------------------------------|------------|
| Height                         | 14 mm      |
| Material of the surface        | galvanised |
| Ø                              | 63 mm      |
| Threaded socket                | yes        |
| Height with thread             | 30 mm      |
| maximum temperature resistance | 120 °C     |
| Thread                         | M8 mm      |
| Weight                         | 240 g      |
| Nominal clamping force         | 350 N      |

|                             |                     |
|-----------------------------|---------------------|
| Material of the magnet core | Ferrite             |
| Type of product             | Flat gripper magnet |