

Flat magnet without thread, Ferrite, Ø: 16mm



Order data

Order number	085910 16
GTIN	2050000964770
Item class	08Q

Description

Version:

Shielded flat magnets with magnetic core made of **hard ferrite**.

- **Galvanised surface.**
- **Temperature-resistant up to maximum 120 °C.**

Application:

For clamping, assembling, incorporation by pressing in / gluing and fixing / holding.

Technical description

Nominal clamping force	18 N
Material of the surface	galvanised
Ø	16 mm
Height	4.5 mm
Weight	4.5 g
maximum temperature resistance	120 °C
Material of the magnet core	Ferrite
Type of product	Flat gripper magnet

