



Pressure regulator 0.5 – 10 bar, Internal thread Ø: 1/2in



Order data

Order number	080012 1/2
GTIN	4047322129404
Item class	08A

Description

Version:

Service units can be made up as required; the coupling pack supplied can be used to add extensions.

Service unit in modular series ("multifix" system), consisting of filter, pressure regulator and mist atomiser. Control range 0.5- 10 bar, operating pressure maximum 16 bar, operating temperature maximum 60 °C.

Advantage:

The service unit can be configured individually, e. g. with several pressure regulators, without oil atomiser (for oil-free tools) etc.

Application:

For systems in the pressure range up to 16 bar. Compatible with the products of CEJN, RECTUS and JWL.

Technical description

Height (H)	248 mm
Internal thread Ø	1/2 in
Flow rate for 3-part service unit	3100 l/min

Overall length (L) as 3-part service unit	202 mm
Type of product	Pressure regulator