

Garant
Boring bar HSS, right-hand, Shank \varnothing / insert size: 8/07mm


Order data

Order number	260328 8/07
GTIN	4062406401061
Item class	21T

Technical description

Clamping height L_2	7 mm
Head length L_1	20 mm
Pack of insert screws	269028 7
Insert size	7 mm
Centre offset L_3	8 mm
ISO code toolholder	AH08K SDQCR/L07
Overall length L	125 mm
Minimum pre-drill $\varnothing D_{\min}$	12 mm
suitable indexable insert	DC.. 0702..
Setting angle κ	107.5 degrees
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

Set of insert screws Type 7

269028 7