

**Garant**
**Boring bar HSS, right-hand, Shank  $\varnothing$  / insert size: 8/07mm**

**Order data**

Order number	260332 8/07
GTIN	4062406401085
Item class	21T

**Technical description**

Overall length L	125 mm
Pack of insert screws	269028 7
Setting angle $\kappa$	93 degrees
Clamping height $L_2$	7 mm
ISO code toolholder	AH08K SDUCR/L07
Minimum pre-drill $\varnothing D_{\min}$	13.5 mm
Overhang $L_1$	40 mm
Insert size	7 mm
suitable indexable insert	DC.. 0702..
Centre offset $L_3$	7.5 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

---

**Accessories**

Set of insert screws Type 7

269028 7

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500