

Garant
Boring bar HSS, left-hand, Shank \varnothing / insert size: 8/07mm

Order data

Order number	260333 8/07
GTIN	4062406401092
Item class	21T

Technical description

Overall length L	125 mm
Clamping height L ₂	7 mm
Centre offset L ₃	7.5 mm
Minimum pre-drill $\varnothing D_{\min}$	13.5 mm
Pack of insert screws	269028 7
suitable indexable insert	DC.. 0702..
ISO code toolholder	AH08K SDUCR/L07
Overhang L ₁	40 mm
Insert size	7 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

Set of insert screws Type 7

269028 7

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500