

Garant GREENPLUS

**GARANT GreenPlus Flex Cleaner, Contents (ml or l): 20****Order data**

Order number	088001 20
GTIN	4062406400873
Item class	01L

**Description****Version:**

NSF certification. Suitable for use in the food industry.

The **flexible degreaser** for quick cleaning of oils, emulsions and greases. Can be mixed with water up to a ratio of 1:10. 20-litre can. If necessary, please order the appropriate discharge valve (No. 088010 size 20-30).

The Flex Cleaner is also suitable for low-foaming use in high-pressure cleaners and floor cleaning systems and thus can be used flexibly wherever foam could be problematic. During cleaning, aluminium and brass surfaces in particular are protected against tarnishing up to 75°C. Temporary corrosion protection is provided by the cleaner. For manual use, spray the cleaning agent and wipe it off with a cloth after a short processing time. When used in the foodstuffs industry, wash the surface with sufficient water after cleaning.

- **Carries no hazard labels.**
- **Can be used manually and with a machine.**
- **NSF-certified for the foodstuffs industry.**
- **For refilling spray bottles and pressure sprayers.**

**Technical description**

Shape	liquid
-------	--------

Colour	transparent
Boiling point	100 °C
Storage temperature	2 - 35 °C
Version	Can
Sustainability	GARANT GreenPlus
pH value	9
Density	1,01 g/cm <sup>3</sup>
Contents	20 l
Series	GreenPlus
Type of product	Universal cleaner

---

## Accessories

GARANT GreenPlusCan discharge valve suitable for can size 20-30 l

088010 20-30