



Side lock arbor with cooling channel bore, HSK-A 63 A = 120, Clamping range Ø D1: 12mm



Order data

Order number	304319 12
GTIN	4062406421984
Item class	32A

Description

Version:

- With RFID/Balluffchip bore.
- HSK mating faces machined.

With coolant supply holes that cannot be plugged.

Application:

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Note:

HSK 40 and 50, Form A and E available ex works by the manufacturer.

Technical description

External Ø D	42 mm
Spare clamping screw No. 30 9900	12
Overhang dimension A	120 mm
Clamping Ø D ₁	12 mm
Adapter	HSK-A 63 A = 120
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1

Arbor standard	DIN 69882-4
Shape	A
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 6.3 at 20,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping Ø D1 12 mm	309900 12
--	-----------