

**Industrial coupling External thread, Connection external thread: 1/2in****Order data**

Order number	080230 1/2
GTIN	4062406403201
Item class	02A

**Description****Version:**

Industrial coupling designed for an optimised high flow rate of 2000 l/min (air), **nominal value 7.8**. High-quality and sturdy quick-release coupling that shuts off on one side. Flow-optimised valve, extremely high flow rates, low pressure drop, long service life, excellent operational reliability and absolute leak-tightness.

Operating pressure: PN 35 bar / temperature: -20 °C to +100 °C.

**Material:**

Nickel-plated brass, sleeve steel hardened and nickel-plated.

**Technical description**

Connection external thread	1/2 in
Flow rate	2000 l/min
Material	Brass
maximum operating pressure	35 bar
Type of product	Coupling

