



## Industrial coupling Hose connection, Hose connection internal Ø (nominal bore): 13mm



### Order data

Order number	080232 13
GTIN	4062406423162
Item class	02A

### Description

#### Version:

Industrial coupling designed for an optimised high flow rate of 2000 l/min (air), **nominal value 7.8**. High-quality and sturdy quick-release coupling that shuts off on one side. Flow-optimised valve, extremely high flow rates, low pressure drop, long service life, excellent operational reliability and absolute leak-tightness.

Operating pressure: PN 35 bar / temperature: -20 °C to +100 °C.

#### Material:

Nickel-plated brass, sleeve steel hardened and nickel-plated.

### Technical description

Flow rate	2000 l/min
maximum operating pressure	35 bar
Material	Brass
Hose connection internal Ø (nominal bore)	13 mm
Type of product	Coupling

