

DYMO**Labelling machine, Type: 5200**

Order data

| | |
|--------------|---------------|
| Order number | 085500 5200 |
| GTIN | 3501170841402 |
| Item class | 08U |

Description**Version:**

Robust portable labelling machines for fast and simple production of self-adhesive plastic labels. Permanent thermal transfer printing. Adjustable tape advance and reverse. Power supply from rechargeable **Li-ion battery**, mains charger. Simple text generation with quick-access buttons. **Robust industrial label printer** for easy labelling of cables, control panels, shelves etc. **Direct access buttons** for frequently-used electro-technical symbols.

Application:

The labels stick to nearly all smooth grease-free surfaces.

Supplied with:

Includes lettering tape black on white and user instructions. Labelling machine incl. lithium-ion battery and power supply unit. 1× nylon tape cartridge, white 19 mm × 3.5 m, 1× industrial vinyl label, white 12 mm × 5.5 m.

Note:

- **Different language versions can be installed.**
- **With German QWERTZ keyboard ex stock, French AZERTY keyboard available on a short lead time.**

Technical description

| | |
|---|------------------------------|
| available tape widths | 9; 12; 19 mm |
| Width | 124 mm |
| Tape cut-off type | manual |
| Number of rechargeable batteries contained | 1 |
| Mains adaptor | including |
| Length | 64 mm |
| Number of available characters/symbols | 100 |
| Special features | Label storage |
| maximum character height | 13 mm |
| Number of lettering styles | 4 |
| Type | Rhino 5200 |
| Type of rechargeable battery | Lithium-ion |
| Number of font widths | 2 |
| Number of font sizes | 7 |
| Keyboard layout | ABC |
| Power supply | Rechargeable battery-powered |
| Number of text lines | 1-4 |
| Height | 234 mm |
| suitable tape cartridge | RHINO |
| Weight including rechargeable battery | 780 g |
| Number of visible characters in the display | 2×14 |
| Packaging | Carrying case |
| Manufacturer's designation | S0841400 |
| Type of product | Labelling machine |

Accessories

| | |
|---|----------|
| Printer ribbon cartridge Type W | 085512 W |
| Printer ribbon cartridge 19 mm×3.5 m nylon Type W | 085516 W |

| | |
|---|----------|
| Printer ribbon cartridge 12 mm × 5.5 m vinyl Type W | 085517 W |
| Printer ribbon cartridge Type W | 085513 W |
| Printer ribbon cartridge 9 mm × 5.5 m vinyl Type W | 085509 W |
| Printer ribbon cartridge Type W | 085511 W |
| Printer ribbon cartridge Type W | 085514 W |
| Printer ribbon cartridge 19 mm × 5.5 m vinyl Type W | 085510 W |