

FLUKE®

**Non-contact voltage testers, Type: 1ACII****Order data**

Order number	473005 1ACII
GTIN	095969290814
Item class	47H

**Description****Version:**

Compact voltage tester for non-contact detection of live conductors.

**Function:**

IP40: Protected against penetration by foreign bodies with  $\varnothing > 1$  mm, however tools and wires should be kept away, and offers no protection against water.

**Application:**

Testing of cables, sockets, junction boxes etc., if voltage is present, the measuring prod lights up red and sounds a beep signal.

**Technical description**

Article no of the battery / rechargeable battery fitted	081561 LR3
Overvoltage category	CAT IV / 1000 V
Power supply	Battery-powered
IP Index of Protection	IP 40
Number of batteries contained	2
Display range AC	200 - 1000 V
Power supply	2× 081561 LR3
Type of product	Voltage tester

**Services**

027120 S

CalibrationVoltage tester Type S	
----------------------------------	--

DAkkS calibrationVoltage tester Type S	027160 S
--	----------

---

**Accessories**

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------