

BENNING**Phase tester, Type: VT2****Order data**

Order number	473282 VT2
GTIN	4014651440555
Item class	47A

Description**Version:**

For quick and easy phase testing at sockets, junction boxes, switches and lamps. Locates cable breaks in insulated cables.

Function:

IP53: Protected against splashed water from directions up to 60° when in normal operating position and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Application:

Phase testing, testing of insulated cables and testing for broken cables. Also magnetic field testing on valves, switches, relays, pumps and magnetic field coils.

Standard:

DIN EN 61010-1.

Supplied with:

2 batteries No. 081561 size LR3.

Technical description

Overvoltage category	CAT III 1000 V; CAT IV 600 V
IP Index of Protection	IP 53
Number of batteries contained	2
Power supply	Battery-powered
Voltage range AC	12 - 1000 V
Article no of the battery / rechargeable battery fitted	081561 LR3
Material of the housing	ABS plastic

Type of product

Phase tester

Accessories

Alkaline-manganese batteries International size LR3

081561 LR3