

BENNING**Digital current clamp, Manufacturer's designation: CM10-1****Order data**

Order number	473305 CM10-1
GTIN	4014651446885
Item class	47A

Description**Version:**

Robust and ergonomic plastic casing with illuminated LCD display. Reliable AC and DC measurements without breaking the operating circuit. Recording of measured value and maximum value, relative measurement.

Application:

Digital service multimeters for a wide range of applications. These provide a high level of safety and other additional functions. For professional use in industry, service and manual crafts. Capacitance measurement, diode testing. Data logger, memory, Bluetooth, app. Switch-on current measurement (INRUSH), low-pass filter (HFR), voltage sensor, ZERO function.

Standard:

IEC / EN 061010-1 (DIN VDE 0411-1).

Supplied with:

Batteries, probe leads, compact protective case, operating instructions.

Technical description

Article no of the battery / rechargeable battery fitted	081561 LR6
Frequency	0.01 Hz – 10 kHz

Basic accuracy	1 %
Measurement process	TRUE RMS
Overvoltage category	CAT IV 600 V
Overvoltage category	CAT IV 600 V
Memory function	HOLD, MAX / MIN
DC current	10 mA – 1500 A
Power supply	Battery-powered
Resistance	0.1 Ω – 600 Ω
acoustic continuity test	yes
maximum jaw aperture	42 mm
DC voltage	0.1 mV – 1000 V
AC voltage	0.1 V – 1000 V
Number of batteries contained	2
Manufacturer's designation	CM10-1
Information displayed	6000
AC current	10 mA – 1500 A
Power supply	2× 081561 LR6
Calibration	I4
Type of product	Current clamp

Services

DAkkS calibrationClamp meter Type D	027060 D
CalibrationClamp meter Type D	027050 D

Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------