

Garant GREENPLUS

## Thread locking 2GP22, Contents: 250ml



### Order data

Order number	088060 250
GTIN	4062406422806
Item class	01K

### Description

#### Version:

The use of thread-lockers prevents the screw fastenings from accidentally releasing and coming undone. The single-component anaerobic thread-lockers are suitable for all thread types and forms. Screw fastenings are sealed. Seizing is reliably prevented.

Type **2GP22** low-strength. Medium viscosity. Ideal for easy-to-remove screw fastenings. For securing screws with fine threads.

#### Application:

**Low strength** – Can be undone with normal tools. **Medium strength** – Can still be undone with normal tools. **High strength** – Can be undone only with special tools or by heating (>150°C).

#### Note:

Clean the material to be worked on in advance with cleaner without hazard labels No. 088004.

### Technical description

Disassembly	with normal tool
minimum break-away torque	5.5 - 11.5 Nm
Suitable for material	Metal
Functional strength to	3 - 6 h

Suitable for application area	Thread locking
Suitable for application area	Thread sealing
Suitable for application area	general purpose use
Strength class	low strength
Characteristics	fluorescent under UV light
Characteristics	sealing
for thread size M to	M36
Storage temperature	5 - 23 °C
Touch dry after	5 - 10 min
Capacity	250 ml
Dynamic viscosity	800 - 1500 mPas
Flashpoint	100 °C
Chemical basis	Methacrylate
Working life after date of manufacture	24 mo
Shape	liquid
Operating temperature range	-55 - 180 °C
Density	1.08 g/cm <sup>3</sup>
for thread types	Fine thread
Colour	violet
Sustainability	GARANT GreenPlus
Series	GreenPlus
Type of product	Thread locking