

Garant GREENPLUS

Thread locking 2GP43, Contents: 50ml



Order data

Order number	088061 50
GTIN	4062406423414
Item class	01K

Description

Version:

The use of thread-lockers prevents the screw fastenings from accidentally releasing and coming undone. The single-component anaerobic thread-lockers are suitable for all thread types and forms. Screw fastenings are sealed. Seizing is reliably prevented.

Type **2GP43** medium-strength. Seals and locks many types of screw fastenings. High resistance to vibrations. Quick curing on a high number of ferrous metals. Increased oil tolerance.

Application:

Low strength – Can be undone with normal tools. **Medium strength** – Can still be undone with normal tools. **High strength** – Can be undone only with special tools or by heating (>150°C).

Note:

Clean the material to be worked on in advance with cleaner without hazard labels No. 088004.

Technical description

Density	1.08 g/cm ³
Functional strength to	3 - 6 h
Strength class	medium strength
Colour	blue

Flashpoint	100 °C
Touch dry after	5 - 15 min
Suitable for application area	general purpose use
Suitable for application area	Thread sealing
Suitable for application area	oily surfaces
Characteristics	fluorescent under UV light
Characteristics	sealing
Characteristics	vibration-resistant
Capacity	50 ml
Suitable for material	Metal
Chemical basis	Methacrylate
minimum break-away torque	15 - 25 Nm
Storage temperature	5 - 23 °C
Shape	liquid
Working life after date of manufacture	24 mo
Operating temperature range	-55 - 180 °C
Dynamic viscosity	1500 - 4000 mPas
Disassembly	with normal tool
for thread size M to	M36
Sustainability	GARANT GreenPlus
Series	GreenPlus
Type of product	Thread locking