

Garant GREENPLUS

Flat gasket sealant 5GP74, Contents: 50ml



Order data

Order number	088067 50
GTIN	4062406423537
Item class	01K

Description

Version:

Sealant that cures when applied as a hermetic seal between close-fitting metal surfaces. Type **5GP74**. For sealing flanges and surfaces. Quick-curing, slightly flexible sealant film.

Note:

Clean the material to be machined in advance with cleaner without hazard labels No. 088004.

Technical description

Strength class	medium strength
Chemical basis	anaerobic methacrylate
Shape	liquid
Operating temperature range	-55 - 180 °C
Storage temperature	5 - 23 °C
Disassembly	with normal tool
Suitable for application area	Flange connection
Suitable for application area	Liquid gasketing

Colour	orange
Density	1.09 g/cm ³
Maximum gap size	0.25 mm
Functional strength to	3 - 6 h
Suitable for material	Metal
Touch dry after	5 - 20 min
Flashpoint	100 °C
Dynamic viscosity	23000 - 35000 mPas
Characteristics	water-resistant
Characteristics	fluorescent under UV light
Working life after date of manufacture	24 mo
minimum break-away torque	10 - 20 Nm
Capacity	50 ml
Sustainability	GARANT GreenPlus
Series	GreenPlus
Type of product	Sealant