



## Clamping head smooth, Top 52, Clamping $\varnothing$ (0.5 mm increments): 13mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 329966 13     |
| GTIN         | 2050002051188 |
| Item class   | 33H           |

### Description

#### Version:

Clamping heads, **round profile, in 0.5 mm increments. Please specify required clamping  $\varnothing$  with order.**

Smooth version for precision machining.

#### Advantage:

- **25% greater clamping force than clamping head RD.**
- **No radial movement between clamping head and clamping element mounting, therefore immune to dirt.**
- **Unique stiffness due to large seating area of the clamping segments.**

#### Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

#### Recommendation:

**Clamping heads for special profiles to your individual requirements on request.**

#### Note:

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

### Technical description

|         |        |
|---------|--------|
| Adapter | Top 52 |
|---------|--------|

Type of product

Clamping head