

Garant GREENPLUS

## Flat gasket sealant 5GP73, Contents: 250ml



### Order data

Order number	088068 250
GTIN	4062406423568
Item class	01K

### Description

#### Version:

Sealant that cures when applied as a hermetic seal between close-fitting metal surfaces. Type **5GP73**. Medium-strength thixotropic surface seal for sealing metallic threaded parts. Sealing of covers, flanges and surfaces. Quick-curing, slightly flexible sealant film.

#### Note:

Clean the material to be machined in advance with cleaner without hazard labels No. 088004.

### Technical description

Chemical basis	anaerobic methacrylate
Characteristics	water-resistant
Characteristics	oil-resistant
Characteristics	fluorescent under UV light
Colour	green
Density	1.11 g/cm <sup>3</sup>
minimum break-away torque	10 - 20 Nm

Dynamic viscosity	35000 - 60000 mPas
Suitable for material	Metal
Touch dry after	5 - 15 min
Maximum gap size	0.2 mm
Strength class	medium strength
Storage temperature	5 - 23 °C
Shape	liquid
Flashpoint	100 °C
Suitable for application area	Flange connection
Suitable for application area	Liquid gasketing
Functional strength to	3 - 6 h
Operating temperature range	-55 - 180 °C
Working life after date of manufacture	24 mo
Capacity	250 ml
Sustainability	GARANT GreenPlus
Series	GreenPlus
Type of product	Sealant