

Garant GREENPLUS

Flat gasket sealant 5GP73, Contents: 50ml



Order data

Order number	088068 50
GTIN	4062406423551
Item class	01K

Description

Version:

Sealant that cures when applied as a hermetic seal between close-fitting metal surfaces. Type **5GP73**. Medium-strength thixotropic surface seal for sealing metallic threaded parts. Sealing of covers, flanges and surfaces. Quick-curing, slightly flexible sealant film.

Note:

Clean the material to be machined in advance with cleaner without hazard labels No. 088004.

Technical description

minimum break-away torque	10 - 20 Nm
Flashpoint	100 °C
Functional strength to	3 - 6 h
Chemical basis	anaerobic methacrylate
Strength class	medium strength
Working life after date of manufacture	24 mo
Storage temperature	5 - 23 °C

Capacity	50 ml
Suitable for application area	Flange connection
Suitable for application area	Liquid gasketing
Suitable for material	Metal
Dynamic viscosity	35000 - 60000 mPas
Touch dry after	5 - 15 min
Colour	green
Shape	liquid
Maximum gap size	0.2 mm
Characteristics	water-resistant
Characteristics	oil-resistant
Characteristics	fluorescent under UV light
Density	1.11 g/cm ³
Operating temperature range	-55 - 180 °C
Sustainability	GARANT GreenPlus
Series	GreenPlus
Type of product	Sealant