

**Clamping head smooth, Top 52, Clamping \varnothing (0.5 mm increments): 48mm****Order data**

| | |
|--------------|---------------|
| Order number | 329966 48 |
| GTIN | 2050002051881 |
| Item class | 33H |

Description**Version:**

Clamping heads, **round profile, in 0.5 mm increments. Please specify required clamping \varnothing with order.**

Smooth version for precision machining.

Advantage:

- **25% greater clamping force than clamping head RD.**
- **No radial movement between clamping head and clamping element mounting, therefore immune to dirt.**
- **Unique stiffness due to large seating area of the clamping segments.**

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Recommendation:

Clamping heads for special profiles to your individual requirements on request.

Note:

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

| | |
|---------|--------|
| Adapter | Top 52 |
|---------|--------|

Type of product

Clamping head