

Garant GREENPLUS

Joint connection 6GP60, Contents: 250ml**Order data**

Order number	088071 250
GTIN	4062406423629
Item class	01K

Description**Version:**

When using joining as a production technique, two or more components are connected through positive contact. When using the adhesive, the full jointing face is used to establish a solid connection. It allows for high force transfer and dynamic loads (high shear strength).

Type **6GP60**. For repair of worn areas and restoring correct fits. Large gap size suitable. Cured product can be machined by drilling, milling or grinding.

Note:

Clean the material to be machined in advance with cleaner without hazard labels No. 088004.

Technical description

Colour	silver
Chemical basis	Methacrylate
Capacity	250 ml
Functional strength to	3 - 6 h
Strength class	high-strength
minimum break-away torque	18 Nm

Dynamic viscosity	200000 - 600000 mPas
Density	1.13 g/cm ³
Touch dry after	5 - 15 min
Working life after date of manufacture	24 mo
Operating temperature range	-55 - 180 °C
Storage temperature	5 - 23 °C
Flashpoint	100 °C
Suitable for application area	Repairs
Suitable for application area	Joint connection
Shape	paste
for thread size M to	M20
Maximum gap size	0.3 mm
Characteristics	mechanically resilient
Characteristics	fluorescent under UV light
Suitable for material	Metal
Sustainability	GARANT GreenPlus
Series	GreenPlus
Type of product	Jointing product