

**LED floodlight, Power consumption: 48W****Order data**

Order number	081274 48
GTIN	5708997354537
Item class	08C

**Description****Version:**

Non-shadowing and non-dazzle version with wide spread of light.

With integrated handle and base for direct mounting of the floodlight. Two Schuko sockets allow the connection of electric tools quickly and easily, without having to additionally use a cable.

**Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

**Suitable for:**

Three-leg stand No. 081252 size 1.35-3.

**Technical description**

Nominal voltage	100 - 240 V
Weight	3430 g
Overall height	310 mm
Beam dispersion angle adjustable	100 degrees
Connection cable length	5 m

Power consumption	48 W
Overall length	318 mm
Power supply	Mains operated
Overall width	117 mm
IP Index of Protection	IP 54
Illumination	6000 lm
Type of product	Area light