



## Pneumatic ratchet screwdriver, Type: 9427



### Order data

Order number	079122 9427
GTIN	015451652111
Item class	03R

### Description

#### Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal  $\varnothing$ . Pneumatic mini ratchet screwdriver with 130 mm overall length. Quick-change button for socket changes.

#### Spare part:

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

### Technical description

maximum speed	270 min <sup>-1</sup>
Compressed air connection	1/4 in
maximum vibration to EN	5 m/s <sup>2</sup>
maximum air consumption	336 l/min
Torque range	7 - 35 Nm
recommended hose size (internal $\varnothing$ )	10 mm
Tool arbor size	3/8 in
Manufacturer's designation	9427

Weight	0.5 kg
Connection thread	BSP
maximum screw $\varnothing$ (8.8 - 12.9)	M8
Length	130 mm
Operating noise	93 dB(A)
Type of product	Screwdriver