



Pneumatic die grinder collet Ø 6 mm long, Type: 9110Q-B



Order data

Order number	079455 9110Q-B
GTIN	015451662141
Item class	03R

Description

Version:

Mini die grinder with high no-load speed for quiet and efficient grinding. Precise power and control due to integrated speed controller.

Supplied with:

Supplied with 1 each of 1/4 inch and 6 mm collet.

Output power: 240 W

maximum speed: 27000 rpm

maximum air consumption: 226 l/min

Connection thread: NPT

Compressed air connection: 1/4 inch

recommended hose size (internal Ø): 10 mm

Technical description

maximum vibration to EN	4.9 m/s ²
recommended hose size (internal Ø)	10 mm
Manufacturer's designation	9110Q-B
Connection thread	NPT
Compressed air connection	1/4 inch
Output power	240 W
Weight	0.7 kg

Operating noise	80 dB(A)
maximum speed	27000 rpm
maximum air consumption	226 l/min
Length	260 mm
Type of product	Straight die grinder