



LED headlamp with rechargeable battery, Type: H7R-CORE



Order data

Order number	081479 H7R-CORE
GTIN	4058205020909
Item class	04B

Description

Version:

Powerful high-performance LED headlamps for professional use.

- **Pivoting head and stepless focussing function.**
- **Intuitive operation and stepless dimming.**
- **Exchangeable and washable head band.**
- **Ledlenser connecting system as a standardised interface permits easy connection with a comprehensive range of accessories.**

Powerful headlamps with intuitive operation and stepless brightness control, extremely high protection against dust and water due to Flex Sealing Technology Ledlenser Connecting System as a standard interface permits easy coupling with a comprehensive range of accessories.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

IP Index of Protection	IP 67
Illumination step 2	15 lm
Illumination	600 lm
Number of rechargeable batteries contained	1

Weight	259 g
Illumination time stage 2	65 h
Manufacturer's designation	H7R Core
Type of rechargeable battery	Lithium-ion
Head Ø	41 mm
Power supply	Rechargeable battery-powered
Illumination time	4 h
Light current boost	1000 lm
Type of product	Headlamp