

Flat magnet with internal thread, Ferrite, Ø: 80mm



Order data

Order number	085915 80
GTIN	2050000965319
Item class	08Q

Description

Version:

- **Shielded flat magnet made of hard ferrite with insert nut.**
- **Galvanised surface.**
- **Temperature-resistant up to maximum 120 °C.**

Application:

For clamping, assembling, incorporation by screw fastening.

Note:

Screw-in hooks with external thread under No. 085921.

Technical description

Height	18 mm
maximum temperature resistance	120 °C
Threaded socket	yes
Nominal clamping force	600 N
Weight	520 g
Ø	80 mm
Material of the surface	galvanised
Thread	M10 mm
Height with thread	34 mm

Material of the magnet core	Ferrite
Type of product	Flat gripper magnet