

Flat magnet with internal thread, Ferrite, Ø: 10mm



Order data

Order number	085915 10
GTIN	2050000964985
Item class	08Q

Description

Version:

- **Shielded flat magnet made of hard ferrite with insert nut.**
- **Galvanised surface.**
- **Temperature-resistant up to maximum 120 °C.**

Application:

For clamping, assembling, incorporation by screw fastening.

Note:

Screw-in hooks with external thread under No. 085921.

Technical description

Ø	10 mm
Material of the surface	galvanised
Thread	M3 mm
Threaded socket	yes
maximum temperature resistance	120 °C
Height	4.5 mm
Nominal clamping force	4 N
Height with thread	11.5 mm
Weight	3 g

Material of the magnet core	Ferrite
Type of product	Flat gripper magnet

Accessories

Screw-in hook set with external thread 10 pieces Thread M3	085921 M3
--	-----------