

**Quick connect With hose connection, Hose internal thread connection Ø: 6mm****Order data**

Order number	080172 6
GTIN	4062406523954
Item class	02A

Description**Version:**

Quick-release couplings nominal value 7.2. Flow rate 1000 l/min (air). Brass material (bright finish). Operating pressure: PN 35 bar / temperature: -20 °C to +100 °C.

Technical description

Hose internal thread connection Ø	6 mm
maximum operating pressure	35 bar
Flow rate	1000 l/min
Type of product	Coupling