



Quick connect With hose connection, Hose internal thread connection Ø: 9mm



Order data

Order number	080172 9
GTIN	4062406523961
Item class	02A

Description

Version:

Quick-release couplings nominal value 7.2. Flow rate 1000 l/min (air). Brass material (bright finish). Operating pressure: PN 35 bar / temperature: -20 °C to +100 °C.

Technical description

Flow rate	1000 l/min
maximum operating pressure	35 bar
Hose internal thread connection Ø	9 mm
Type of product	Coupling