



## Quick connect With hose connection, Hose internal thread connection Ø: 13mm



### Order data

Order number	080172 13
GTIN	4062406523978
Item class	02A

### Description

#### Version:

Quick-release couplings nominal value 7.2. Flow rate 1000 l/min (air). Brass material (bright finish). Operating pressure: PN 35 bar / temperature: -20 °C to +100 °C.

### Technical description

maximum operating pressure	35 bar
Flow rate	1000 l/min
Hose internal thread connection Ø	13 mm
Type of product	Coupling