

**Nipple pack with internal thread 10 pieces, Connection internal thread: 3/8in****Order data**

Order number	080173 3/8
GTIN	4062406522537
Item class	02A

Description**Version:**

Quick-release couplings nominal value 7.2. Flow rate 1000 l/min (air). Brass material (bright finish). Operating pressure: PN 35 bar / temperature: -20 °C to +100 °C.

Technical description

maximum operating pressure	35 bar
Set contents	10
Connection external thread	3/8 in
Type of product	Nipple