

**HOLEX****Hose coupling adaptor set 10 pieces, Hose internal thread connection Ø: 13mm****Order data**

Order number	080176 13
GTIN	4062406522599
Item class	02A

**Description****Version:**

Quick-release couplings nominal value 7.2. Flow rate 1000 l/min (air). Brass material (bright finish). Operating pressure: PN 35 bar / temperature: -20 °C to +100 °C.

**Technical description**

Hose internal thread connection Ø	13 mm
maximum operating pressure	35 bar
Set contents	10
Type of product	Nipple