

**Hose coupling adaptor set 10 pieces, Hose internal thread connection Ø: 9mm****Order data**

Order number	080176 9
GTIN	4062406522582
Item class	02A

Description**Version:**

Quick-release couplings nominal value 7.2. Flow rate 1000 l/min (air). Brass material (bright finish). Operating pressure: PN 35 bar / temperature: -20 °C to +100 °C.

Technical description

Set contents	10
maximum operating pressure	35 bar
Hose internal thread connection Ø	9 mm
Type of product	Nipple