


Side lock arbor Form AD, SK 50 A = 130, Clamping range \varnothing D1: 6mm

Order data

Order number	300347 6
GTIN	4062406420956
Item class	32A

Description
Version:

With Balluff/RFID chip bore.

All shanks fine bead blasted. Balancing quality G 6.3 / 18,000 rpm.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Clamping \varnothing D ₁	6 mm
Overhang dimension A	130 mm
Spare clamping screw No. 30 9900	6
External \varnothing D	25 mm
Adapter	SK 50 A = 130
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 6.3 at 18,000 rpm
Concentricity	$\leq 3 \mu\text{m}$

Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping \varnothing D1 6 mm	309900 6
---	----------