


**Side lock arbor Form AD, SK 50 A = 130, Clamping range  $\varnothing$  D1: 12mm**

**Order data**

Order number	300347 12
GTIN	4062406420987
Item class	32A

**Description**
**Version:**

With Balluff/RFID chip bore.

All shanks fine bead blasted. Balancing quality G 6.3 / 18,000 rpm.

**Application:**

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

**Technical description**

Clamping $\varnothing$ D <sub>1</sub>	12 mm
Spare clamping screw No. 30 9900	12
Overhang dimension A	130 mm
External $\varnothing$ D	42 mm
Adapter	SK 50 A = 130
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 6.3 at 18,000 rpm
Concentricity	$\leq 3 \mu\text{m}$

Machining strategy	HPC
Type of product	Side lock arbor

---

## Accessories

Spare clamping screw for chucks with clamping $\varnothing$ D1 12 mm	309900 12
----------------------------------------------------------------------	-----------