

Garant

PU coiled hose 1/4 inch with steel safety coupling Ø 8 × 12 mm, usable hose length: 5m

**Order data**

Order number	080238 5
GTIN	4062406523763
Item class	01A

Description**Version:**

Very light, flexible, and abrasion-resistant PU spiral hose with good spring retention. Temperature-resistant from -20 / 60 °C.

Supplied with:

Includes **GARANT steel safety quick-change coupling** and steel coupling adaptor.

Technical description

maximum operating pressure	10 bar
Hose internal Ø	8 mm
Hose external Ø	12 mm
Temperature range	-20 - 60 °C
usable hose length	5 m
Type of product	Hose

