

**Garant**

**PU coiled hose 1/4 inch with steel safety coupling Ø 8 × 12 mm, usable hose length: 3m**

**Order data**

Order number	080238 3
GTIN	4062406523756
Item class	01A

**Description****Version:**

Very light, flexible, and abrasion-resistant PU spiral hose with good spring retention. Temperature-resistant from -20 / 60 °C.

**Supplied with:**

Includes **GARANT steel safety quick-change coupling** and steel coupling adaptor.

**Technical description**

Hose internal Ø	8 mm
Temperature range	-20 - 60 °C
usable hose length	3 m
maximum operating pressure	10 bar
Hose external Ø	12 mm
Type of product	Hose

