

Garant

PU coiled hose 1/2 inch with steel safety coupling Ø 11 × 16 mm, usable hose length: 5m

**Order data**

Order number	080239 5
GTIN	4062406523787
Item class	01A

Description**Version:**

Very light, flexible, and abrasion-resistant PU spiral hose with good spring retention. Temperature-resistant from -20 / 60 °C.

Supplied with:

Includes **GARANT steel safety quick-change coupling** and steel coupling adaptor.

Technical description

maximum operating pressure	10 bar
usable hose length	5 m
Hose external Ø	16 mm
Hose internal Ø	11 mm
Temperature range	-20 - 60 °C
Type of product	Hose

