

Garant

PU coiled hose 1/2 inch with steel safety coupling Ø 11 × 16 mm, usable hose length: 3m

**Order data**

Order number	080239 3
GTIN	4062406523770
Item class	01A

Description**Version:**

Very light, flexible, and abrasion-resistant PU spiral hose with good spring retention. Temperature-resistant from -20 / 60 °C.

Supplied with:

Includes **GARANT steel safety quick-change coupling** and steel coupling adaptor.

Technical description

maximum operating pressure	10 bar
Temperature range	-20 - 60 °C
Hose internal Ø	11 mm
Hose external Ø	16 mm
usable hose length	3 m
Type of product	Hose

