



## Attachment eye Quick Lift DSR, Thread $\varnothing$ : M10X1,5



### Order data

Order number	086454 M10X1,5
GTIN	2050002053830
Item class	08Y

### Description

#### Version:

Compact, high-strength steel Quick Lift DSR attachment eye for screwing in. Rotates 360°, pivots 180°. Time saving of up to 80% compared with screwing in a traditional attachment eye (DSR vs. Quick Lift DSR). **Can be rotated under load.** Easy to use as the system is purely mechanical. Maintenance-free, safe and reliable. The Quick Lift DSR can be fastened in the internal thread in seconds by pressing in the screw head. This is a purely mechanical process based on actuating a spring.

#### Note:

**SF 5:1 = Safety Factor 5.**

### Technical description

Weight	0.3 kg
Height of centre divider B	30 mm
Internal hexagon size across flats S	18 mm
Thread $\varnothing$	M10x1.5

Height of screw head A	31 mm
Screw head $\varnothing$ C	30 mm
Lifting capacity WLL SF 5:1	0.4 t
Thread length L	19.5 mm
Eye width E	27 mm
Attachment eye width G	53 mm
Eye thickness F	14 mm
Distance from centre divider to eye D	38 mm
Type of product	Attachment eye