



## Attachment eye Quick Lift DSR, Thread $\varnothing$ : M20X2,5



### Order data

Order number	086454 M20X2,5
GTIN	2050002053878
Item class	08Y

### Description

#### Version:

Compact, high-strength steel Quick Lift DSR attachment eye for screwing in. Rotates 360°, pivots 180°. Time saving of up to 80% compared with screwing in a traditional attachment eye (DSR vs. Quick Lift DSR). **Can be rotated under load.** Easy to use as the system is purely mechanical. Maintenance-free, safe and reliable. The Quick Lift DSR can be fastened in the internal thread in seconds by pressing in the screw head. This is a purely mechanical process based on actuating a spring.

#### Note:

**SF 5:1 = Safety Factor 5.**

### Technical description

Height of screw head A	55 mm
Thread length L	30 mm
Eye width E	55 mm
Thread $\varnothing$	M20x2.5

Height of centre divider B	55 mm
Screw head Ø C	60 mm
Internal hexagon size across flats S	40 mm
Distance from centre divider to eye D	83 mm
Eye thickness F	25 mm
Weight	2.6 kg
Attachment eye width G	115 mm
Lifting capacity WLL SF 5:1	1.7 t
Type of product	Attachment eye