



Attachment eye Quick Lift DSR, Thread \varnothing : M8X1,25



Order data

| | |
|--------------|----------------|
| Order number | 086454 M8X1,25 |
| GTIN | 2050002053823 |
| Item class | 08Y |

Description

Version:

Compact, high-strength steel Quick Lift DSR attachment eye for screwing in. Rotates 360°, pivots 180°. Time saving of up to 80% compared with screwing in a traditional attachment eye (DSR vs. Quick Lift DSR). **Can be rotated under load.** Easy to use as the system is purely mechanical. Maintenance-free, safe and reliable. The Quick Lift DSR can be fastened in the internal thread in seconds by pressing in the screw head. This is a purely mechanical process based on actuating a spring.

Note:

SF 5:1 = Safety Factor 5.

Technical description

| | |
|--------------------------------------|---------|
| Internal hexagon size across flats S | 18 mm |
| Thread length L | 17.5 mm |
| Eye thickness F | 14 mm |
| Height of screw head A | 31 mm |

| | |
|---------------------------------------|----------------|
| Height of centre divider B | 30 mm |
| Eye width E | 27 mm |
| Lifting capacity WLL SF 5:1 | 0.25 t |
| Weight | 0.3 kg |
| Attachment eye width G | 53 mm |
| Distance from centre divider to eye D | 38 mm |
| Thread Ø | M8×1.25 |
| Screw head Ø C | 30 mm |
| Type of product | Attachment eye |